



# widex mind<sup>™</sup> 330

the pleasure of hearing

*Sound Mind. Sound Body.*  
Better Hearing Never Sounded This Good!



## *The pleasure of hearing*

### **Widex proudly introduces the Mind330 hearing aid series.**

Mind330 was designed with focus on the pleasure of hearing through ease, comfort and exceptional sound.

The result is advanced hearing technology and a series of features that bring you a full world of sounds - simply and automatically.

#### **Dual ISP**

The core of the Mind330 is an upgrade of our famous Integrated Signal Processing technology. We call this new technology Dual ISP, and it has been specifically developed to provide comfortable hearing in even more challenging environments.

Before sound reaches your ears, all information about your hearing loss and your immediate listening situation is gathered and assessed. According to your hearing needs and preferences, sound is then processed to ensure the best possible quality.

And wherever you are, whatever environment you are in, Dual ISP allows Mind330 to have the best opportunity to adjust accordingly.

## *Exceptional sound*

Mind330 by Widex is the result of over a half century of research, development and patient's experiences. The mind series of hearing aids provides significant benchmarks to help make your listening experience truly exceptional.

#### **ClearBand**

In the music world, two-way speakers are the preferred solution for providing the best sound over the entire range of tones. By using two separate receiver membranes, one can be dedicated to low-pitched tones and one to high-pitched tones. But two membranes take up more space than one, making it impractical for hearing aid design - until now.

A special feature of the Mind330 m-CB model, the ClearBand hi-fi two-way receiver incorporates two separate membranes in one small unit. This new technology provides you with a broader range of sounds and exceptionally clear and natural sound quality.

#### **Audibility Extender**

The details in speech and environmental sounds are important factors for exceptional sound and comfortable listening. But high-pitched details in, for example, music, or the chirping of birds are often lost as a result of hearing loss.

The **Audibility Extender** works to automatically transpose such sounds into your hearing range. Even lost details in speech can be easier to hear. The result is a fuller sound with more detail.

#### **TruSound**

**Balanced focus of sound.** The TruSound compression system helps to ensure that changing between sound environments is made as smooth and as fast as possible. The philosophy is that:

- soft sounds, such as dripping water, must be audible but remain soft in character
- normal speech, such as face-to-face conversation, must be audible and intelligible
- loud sounds, such as in a crowd, should be heard but not uncomfortable to listen to.

Call your Hearing Healthcare Professional today and ask about the **Widex Mind330**.<sup>v</sup>

**WIDEX**<sup>®</sup>  
High Definition Hearing



## Ease and comfort

While exceptional sound is important, hearing aid wearers also name ease and comfort as essential criteria for full listening satisfaction. The Mind330 series by Widex lives up to these expectations through a specifically tailored master program and features such as SmartSpeak.

### Master program

The master program in a hearing aid is the standard set of parameters that control the sound and performance of the hearing aid. The master program in Mind330 is designed to meet the typical user's wish to be able to enjoy soft environmental sounds, hear speech in varied surroundings and feel comfortable in noisy places.

According to the parameters in the master program, the Mind330 adapts smoothly and automatically to each and every environment you find yourself in during the day - for easy listening comfort.

### Models

Mind330 is available in a wide range of different models to suit most types of hearing loss. From discreet micro, mini and power BTE's to a CIC and an ITE, the Mind330 series has a model for you.

## SmartSpeak

For many patients, it can be difficult remembering how to change settings or programs. With the easy-to-use SmartSpeak feature, Mind330 takes the guesswork out of controlling your hearing aid.

SmartSpeak uses actual recorded speech to tell you of Mind330 functions. For example, when your battery is running low, SmartSpeak will warn you. And if you switch to another program, SmartSpeak will tell you exactly which program you have chosen. These clear, simple to hear, verbal messages come in a wide variety of languages.

Another option is SmartTone, where beep-tones indicate use of chosen hearing aid functions rather than the verbal message.

## mind330 by Widex

### Benefits

### Technical Description

#### Hear More

**Dual ISP** (Integrated Signal Processing) *builds upon* the greatest technology ever put inside a hearing instrument. And an innovative feature like the **Audibility Extender** works to help you hear high pitched sounds like a young child's voice or the beeps of a microwave oven or coffee maker you may not have heard in years!

#### Hear Better

**High Definition Clarity** and maximum strength sound quality! The **TruSound System** captures and preserves the naturalness of sounds – *including speech*. Loud sounds are more comfortable and soft sounds are more audible.

#### Improved Speech Understanding in Noise

*Mind* hearing aids offer an **Advanced High Definition Locator** and **Speech Enhancer** for improved speech understanding in noise.

#### Control

With **SmartSpeak**, your *Mind* hearing aids verbally tell you what they are doing in your choice of 22 major languages! And an **Optional Remote Control** gives you discreet adjustment of multiple programs.

#### Cancel Feedback

**Multi-Directional Active Feedback Cancelling System** stops hearing aid whistling.

#### Longer Battery Life

**EcoTech II Technology** for low current drain and longer battery life.

#### Be Comfortable

**Open-Ear thin tube micro-sized models available** for discreet and comfortable wear.

#### Be Stylish

**Available in a variety of colors.**

#### Protect Your Investment

**Nanocare Wax Protection System** is a state-of-the-art way to protect your valuable in-the-ear and completely-in-the-canal hearing aids from wax and moisture damage.

**widex mind 330**<sup>™</sup>  
the pleasure of hearing